



Prevailing torque type hexagon nut with non-metallic insert DIN 985 Steel Zinc plated [5] M24

Article number	12300.240.001
Brand	-
UBB	950355116829
UNSPSC	31161727
EAN	8715492576941
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M24
Class	[5]
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	985
ISO	≈10511
NF	E25-412

Technical Specification

d-D	M24
h	24
P	3
s	36

Technical Drawing

