



Prevailing torque type hexagon nut with non-metallic insert DIN 985 Steel Zinc plated |5| M30

Article number	12300.300.001
Brand	-
UBB	950355117082
UNSPSC	31161727
EAN	8715492576965
PKG. of 10	Full Box Only

Technical Parameters

Diameter (d-D)	M30
Class	5
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	985
ISO	≈10511
NF	E25-412

Technical Specification

h	30
P	3.50
s	46

Technical Drawing

