



Prevailing torque type hexagon nut with non-metallic insert DIN 985 Steel Zinc plated |8| M8

Article No.	12348.080.001
Brand	-
UBB	951355382056
UNSPSC	31161727
EAN	8715493855687
PKG. of 250	Full Box Only

Technical Parameters

Diameter (d-D)	M8
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-412
ISO	≈10511
DIN	985

Technical Specification

h	8
P	1.25
s	13

Technical Drawing

