



Prevailing torque type hexagon nut with non- metallic insert DIN 985 Steel Zinc plated |8| M12

Article No.	12348.120.001
Brand	-
UBB	951355382213
UNSPSC	31161727
EAN	8715493855700
PKG. of 100	Full Box Only

Technical Parameters

Diameter (d-D)	M12
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	985
ISO	≈10511
NF	E25-412

Technical Specification

h	12
P	1.75
s	19

Technical Drawing

