



## Prevailing torque type hexagon nut with non-metallic insert DIN 985 Steel Zinc plated |10| M14

Article number	12410.140.001
Brand	-
UBB	950355543022
UNSPSC	31161727
EAN	8715492578532
PKG. of 100	Full Box Only

### Technical Parameters

Diameter (d-D)	M14
Class	10
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

### Standards

ISO	≈10511
DIN	985
NF	E25-412

### Technical Specification

h	14
P	2
s	22

### Technical Drawing

