



Prevailing torque type hexagon nut with non-metallic insert DIN 985 Steel Zinc plated |10| M27

Article number	12410.270.001
Brand	-
UBB	950355978061
UNSPSC	31161727
EAN	8715492578594
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M27
Class	10
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-412
ISO	≈10511
DIN	985

Technical Specification

d-D	M27
h	27
P	3
s	41

Technical Drawing

