



Prevailing torque type hexagon nut with non- metallic insert MF DIN 985 Steel Zinc plated yellow passivated |10| M12X1,50

Article number	12422.120.150
Brand	-
UBB	950355655891
UNSPSC	31161727
EAN	8715492578631
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M12
Class	10
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric fine thread

Standards

DIN	985
NF	E25-412
ISO	10512

Technical Specification

d-D	M12
h	12
P	1.5
s	19

Technical Drawing

