



Prevailing torque type hexagon nut with non-metallic insert MF DIN 985 Steel Zinc plated yellow passivated |10| M24X1,50

Article number	12422.240.150
Brand	-
UBB	950355656394
UNSPSC	31161727
EAN	8715492578686
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M24
Class	10
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated yellow passivated
Thread	Metric fine thread

Standards

DIN	985
ISO	10512
NF	E25-412

Technical Specification

d-D	M24
h	24
P	1.5
s	36

Technical Drawing

