



Prevailing torque type hexagon nut with plastic insert, high type ISO 7040 Steel Zinc plated 8 M8

Article number	12510.080.001
Brand	-
UBB	500650979049
UNSPSC	31162400
EAN	8717077312432
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M8
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	6924
ISO	7040

Technical Specification

d-D	M8
h (max.)	9.5
P	1.25
s	13

Technical Drawing

