



Prevailing torque type hexagon nut with non-metallic insert, high type DIN 982 Steel Zinc plated 8 M8

Article number	12600.080.001
Brand	-
UBB	950355135142
UNSPSC	31161727
EAN	8715492579485
PKG. of 250	Full Box Only

Technical Parameters

Diameter	M8
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	≈E25-409
DIN	982
ISO	≈7040

Technical Specification

d-D	M8
h	9.5
P	1.25
s	13

Technical Drawing

