



Prevailing torque type hexagon nut with non-metallic insert, high type DIN 982 Steel Zinc plated 8 M10

Article number	12600.100.001
----------------	---------------

Brand	-
-------	---

UBB	950355135225
-----	--------------

UNSPSC	31161727
--------	----------

EAN	8715492579492
-----	---------------

PKG. of 200	Full Box Only
-------------	---------------

Technical Parameters

Diameter (d-D)	M10
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

ISO	≈7040
DIN	982
NF	≈E25-409

Technical Specification

h	11.5
P	1.50
s	17

Technical Drawing

