



## Prevailing torque type hexagon nut with non-metallic insert, high type DIN 982 Steel Zinc plated 8 M12

Article number	12600.120.001
Brand	-
UBB	950355135308
UNSPSC	31161727
EAN	8715492579508
PKG. of 100	Full Box Only

### Technical Parameters

Diameter (d-D)	M12
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

### Standards

DIN	982
NF	≈E25-409
ISO	≈7040

### Technical Specification

h	14
P	1.75
s	19

### Technical Drawing

