



Prevailing torque type hexagon nut, all metal DIN 980V Steel Zinc plated 8 M10

Article number	12858.100.001
Brand	-
UBB	950355778735
UNSPSC	31161727
EAN	8715492579980
PKG. of 200	Full Box Only

Technical Parameters

Diameter (d-D)	M10
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-410
BS	4929-1
ISO	7042
DIN	980V

Technical Specification

h (max.)	10
P	1.50
s	17

Technical Drawing

