



Prevailing torque type hexagon nut, all metal DIN 980V Steel Zinc plated 8 M18

Article number	12858.180.001
Brand	-
UBB	951355011614
UNSPSC	31161727
EAN	8715492580023
PKG. of 25	Full Box Only

Technical Parameters

Diameter (d-D)	M18
Class	8
Driving features	Hexagon
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	980V
ISO	7042
BS	4929-1
NF	E25-410

Technical Specification

h (max.)	18
P	2.50
s	27

Technical Drawing

