



Eye bolt fully threaded DIN 444 LB Steel Zinc plated 4.6 M20X130

Article number	16182.200.130
Brand	-
UBB	500644872219
UNSPSC	31161610
EAN	8717077035829
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M20
Length	130 mm
Class	4.6
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	444-LB
-----	--------

Technical Specification

d-D	M20
d2(H9)	18
d3 (max.)	40
L (mm)	130
Lg (max.)	32
P	2.5
s (max.)	22

Technical Drawing

