



T-head bolt with nut DIN 261/555 Steel Plain 4.6 M10X60

Article number	16191.100.060
Brand	-
UBB	500650988453
UNSPSC	31162400
EAN	8717077313378
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M10
Length	60 mm
Class	4.6
Head shape	T head
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

DIN	261/555
-----	---------

Technical Specification

b	26
d-D	M10
ds (max.)	10.58
k (nom.)	7
L (mm)	60
m1	21
m2	8
n	10
P	1.5
s	17

Technical Drawing

