



Knurled nut, high type DIN 466 Steel Zinc plated M10

Article number	16680.100.001
Brand	-
UBB	950355177136
UNSPSC	31161729
EAN	8715492592804
PKG. of 10	Full Box Only

Technical Parameters

Diameter	M10
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	466
-----	-----

Technical Specification

d-D	M10
dk	36
ds	20
h	23
k	8
P	1.5

Technical Drawing

