



Knurled nut, high type DIN 466 Steel Zinc plated M12

Article number	16680.120.001
Brand	-
UBB	500644877838
UNSPSC	31161729
EAN	8717077037182
PKG. of 25	Full Box Only

Technical Parameters

Diameter	M12
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	466
-----	-----

Technical Specification

d-D	M12
dk	36
ds	24
h	23
k	10
P	1.75

Technical Drawing

