



## D (chain) shackle DIN 82101 A Steel Hot dip galvanized 11MM

|                |               |
|----------------|---------------|
| Article number | 16813.110.001 |
| Brand          | -             |
| UBB            | 950465004196  |
| UNSPSC         | 31162803      |
| EAN            | 8715492593351 |
| PKG. of 25     | Full Box Only |

### Technical Parameters

|                   |                                                                                                                                                                       |
|-------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Diameter          | 11 mm                                                                                                                                                                 |
| Material          | Steel                                                                                                                                                                 |
| Surface treatment | Zinc plated                                                                                                                                                           |
| Info              | Depending on availability these D (chain) shackles are either zinc plated or hot dip galvanized, and dimensions may deviate. Not to be used for lifting applications. |

### Standards

|     |         |
|-----|---------|
| DIN | 82101-A |
|-----|---------|

### Technical Specification

|        |    |
|--------|----|
| b      | 22 |
| d2     | 11 |
| D (mm) | 11 |
| h      | 42 |

### Technical Drawing

