



Steel Zinc plated M4X40

Article number	17123.040.040
Brand	-
UBB	950370013027
UNSPSC	31161610
EAN	8712547015417
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M4
Length	40 mm
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

Technical Specification

d-D	M4
d2	3.45
h	15
L (mm)	40
P	0.7

Technical Drawing

