



Steel Zinc plated M5X50

Article number	17123.050.050
Brand	-
UBB	950370013100
UNSPSC	31161610
EAN	8712547015424
PKG. of 100	Full Box Only

Technical Parameters

Diameter	M5
Length	50 mm
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread

Standards

Technical Specification

d-D	M5
d2	4.4
h	20
L (mm)	50
P	0.8

Technical Drawing

