



## U-Bolt type B Steel Zinc plated M10X112X89X40

Article number	17243.100.089
Brand	-
UBB	408373268635
UNSPSC	31161616
EAN	8712547003995
PKG. of 25	Full Box Only

### Technical Parameters

b	40
Diameter (d-D)	M10
e	89
h	112
Length (L) (mm)	112
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Type no.	40G

### Standards

### Technical Specification

b	40
D (nom. inch)	2.1/2
D (nom. mm)	76
e	89

### Technical Drawing

