



Screw eye Steel Zinc plated M10X40X15

Article number	17420.104.014
Brand	-
UBB	950370025997
UNSPSC	31161610
EAN	8712547008693
PKG. of 50	Full Box Only

Technical Parameters

D	15
d ₁	M10
Diameter (d-D)	M10
Eye diameter	15
Length (L) (mm)	40
Material	Steel
Surface treatment	Zinc plated
Thread	Metric thread
Type no.	111G

Standards

Technical Specification

d ₂	8.85
P	1.50

Technical Drawing

