

Swiss Tech Slot drill 3 flute DIN 327 Regular Cobalt HSS Uncoated 10,0MM



Article No.	1A119023
Brand	-
UBB	500650047698
UNSPSC	27110000
EAN	5036140205819
PKG. of 1	Full Box Only

Technical Parameters

Flute length	22
Number of flutes	3
Shank diameter tolerance	h6
Coolant delivery	External
Basic material	Cobalt HSS
Material grade	M42
Cutter diameter	10
Plunge type	Centre cutting
Reach type	Standard Neck
Length type	Regular
Milling application	Slotting, Profiling, Semi-finishing, Finishing
Material application	Carbon Steel, Alloy Steel, Copper, Aluminium
Helix direction	Right
Cutter diameter tolerance	e8
Number of cutting ends	1
End mill type	Slot Drill
Coating	Uncoated
Cutting direction	Right
Flute type	Helical

Standards

DIN	844, 1835B
-----	------------

Helix angle 30

Total length (mm) 72

Shank size (mm) 10

Shank type Threaded

STANDARD
IN FASTENING SOLUTIONS

UP COURSE