

Brady Pre-printed GHS/ CLP Chemical Label B30-261-7569-CLP4B 270PC



Article number	1M869440
Brand	-
UBB	500671616414
UNSPSC	46180000
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Color	Red/White
Width (mm)	75
Adhesive component	Permanent Acrylic
Basic material	Vinyl
Brady material number	B-7569
Layout	L4B
Legend	Pre-printed GHS/ CLP Chemical Labels for BBP3X/ S3XXX/i3300 Printers
Max. service temp. °C	75 °C
Min. service temp. °C	-20 °C
Print technology	Thermal Transfer
Printer compatibility	BBP30; BBP31; BBP33; BBP35; BBP37
Ribbon series	B30-R10000
Industry	Facility & Safety Identification
Content (pcs)	270
Finish	Gloss

Standards

Finish	Glanz
Finish	luciu
Finish	Polysk
Finish	Brillo
Finish	Lesk
Finish	Glanzend
Finish	Glossza
Finish	Gloss
Finish	lesk
Application method	Facility & Safety Identification; Hazardous Substance Identification
Height (mm)	110
Length (L) (mm)	75
Thickness	0.102
Type nr.	B-7569
Weight (g)	1009

UR COURSE

BE THE STANDARD
IN FASTENING SOLUTIONS