



Brady Icon A045R-250X250-PE

Article number	10371687
Brand	-
UBB	500671792967
UNSPSC	46180000
EAN	
PKG. of 1	Full Box Only

Technical Parameters

Color	White/Red
Width (mm)	250
Adhesive component	Permanent Acrylic
Basic material	Laminated Polyester
Brady material number	B-7541
Country	EMEA
Legend	ISO Safety Sign - Direction arrow 45° (90° increments), safe condition
Legend language	Global
Max. service temp. °C	110 °C
Min. service temp. °C	-40 °C
PIC description	Direction arrow 45°, top right corner
Product regulations	ISO 7010
Sign type	Fire Fighting
Content (pcs)	1
Number of holes	0
Finish	Gloss
Finish	Glanz

Standards

Finish	luciu
Finish	Połysk
Finish	Brillo
Finish	Lesk
Finish	Glanzend
Finish	Glossza
Finish	Gloss
Finish	lesk
Application method	Facility & safety identification
Height (mm)	250
Length (L) (mm)	250
Thickness	0.099
Type nr.	B-7541
Weight (g)	21
Shape	Square

UP COURSE

THE STANDARD
IN FASTENING SOLUTIONS