

Threaded rod DIN 976-1A Steel Zinc plated 10.9 1 meter M5



| | |
|----------------|---------------|
| Article number | 20135.050.001 |
| Brand | - |
| UBB | 500648373420 |
| UNSPSC | 31161618 |
| EAN | 8717077217874 |
| PKG. of 1 | Full Box Only |

Technical Parameters

| | |
|-------------------|---|
| Length (L) (mm) | 1000 |
| Diameter (d-D) | M5 |
| Class | 10.9 |
| Extra info | 1 meter |
| Material | Steel |
| Thread direction | Right |
| Surface treatment | Zinc plated |
| Thread | Metric thread |
| Info | Warning: electroplating of these products may cause hydrogen embrittlement. |

Standards

| | |
|-----|---------|
| DIN | 976-1A |
| NF | E25-136 |

Technical Specification

| | |
|---|------|
| P | 0.80 |
|---|------|

Technical Drawing

