

Threaded rod DIN 976-1A Steel Zinc plated 10.9 1 meter M12



Article number	20135.120.001
Brand	-
UBB	500648373834
UNSPSC	31161618
EAN	8717077217911
PKG. of 1	Full Box Only

Technical Parameters

Length (L) (mm)	1000
Diameter (d-D)	M12
Class	10.9
Extra info	1 meter
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread
Info	Warning: electroplating of these products may cause hydrogen embrittlement.

Standards

DIN	976-1A
NF	E25-136

Technical Specification

P	1.75
---	------

Technical Drawing

