



## Threaded rod length 3 meter oversized thread DIN 976-1A Steel Hot dip galvanized 4.8 M12

Article number	20147.120.001
Brand	-
UBB	500621925592
UNSPSC	31161618
EAN	8715494514965
PKG. of 1	Full Box Only

### Technical Parameters

Diameter	M12
Length	3000 mm
Class	4.8
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

**Info**

Oversized hot dip galvanized threaded rods are manufactured with standard thread tolerance class 6g before coating. After galvanizing they will therefore NOT fit into standard nuts or threaded holes with thread tolerance class 6H. Suitable nuts have been tapped with thread tolerance class 6AZ (oversized). 3 meter oversized

### Standards

NF	E25-136
DIN	976-1A

d-D	M12
L (mm)	3000
P	1.75

**FABORY**

