



Threaded rod length 1 meter oversized thread DIN 976-1A Steel Hot dip galvanized 8.8 M36

Article number	20150.360.001
Brand	-
UBB	950353602960
UNSPSC	31161618
EAN	8715492604781
PKG. of 2	Full Box Only

Technical Parameters

Diameter	M36
Length	1000 mm
Class	8.8
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread

Info

Oversized hot dip galvanized threaded rods are manufactured with standard thread tolerance class 6g before coating. After galvanizing they will therefore NOT fit into standard nuts or threaded holes with thread tolerance class 6H. Suitable nuts have been tapped with thread tolerance class 6AZ (oversized). 1 meter oversized

Standards

NF	E25-136
DIN	976-1A

d-D	M36
L (mm)	1000
P	4

