



Threaded rod length 1 meter ISO-Metric thread DIN 976-1A Steel Hot dip galvanized 4.8 M16

Article number	20160.160.001
Brand	-
UBB	950353454875
UNSPSC	31161618
EAN	8715492604811
PKG. of 5	Full Box Only

Technical Parameters

Diameter	M16
Length	1000 mm
Class	4.8
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread
Info	ISO metric hot dip galvanized threaded rods are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H.1 meter ISO-metric

Standards

DIN	976-1A
NF	E25-136

Technical Specification

d-D	M16
L (mm)	1000
P	2

Technical Drawing

FABORY

