



Threaded rod length 1 meter ISO-Metric thread DIN 976-1A Steel Hot dip galvanized 8.8 M20

Article number	20170.200.001
Brand	-
UBB	950353455377
UNSPSC	31161618
EAN	8715492604903
PKG. of 3	Full Box Only

Technical Parameters

Diameter	M20
Length	1000 mm
Class	8.8
Material	Steel
Thread direction	Right
Surface treatment	Hot dip galvanized
Thread	Metric thread
Info	ISO metric hot dip galvanized threaded rods are manufactured with thread tolerance class 6az (undersize) before coating. After galvanizing they will fit into standard nuts and threaded holes with thread tolerance class 6H.1 meter ISO-metric

Standards

NF	E25-136
DIN	976-1A

Technical Specification

d-D	M20
L (mm)	1000
P	2.5

Technical Drawing

FABORY

