

Threaded rod length 1 meter DIN 976-1A Steel Plain 8.8 M12



Article number	20220.120.001
Brand	-
UBB	950353010685
UNSPSC	31161618
EAN	8715492605603
PKG. of 5	Full Box Only

Technical Parameters

Length (L) (mm)	1000
Diameter (d-D)	M12
Class	8.8
Extra info	1 meter
Material	Steel
Thread direction	Right
Surface treatment	Plain
Thread	Metric thread

Standards

NF	E25-136
DIN	976-1A

Technical Specification

P	1.75
---	------

Technical Drawing

