

Threaded rod length 1 meter DIN 976-1A Steel Zinc plated 8.8 M5



Article No.	20230.050.001
Brand	-
UBB	950353012335
UNSPSC	31161618
EAN	8715492605795
PKG. of 10	Full Box Only

Technical Parameters

Length (L) (mm)	1000
Diameter (d-D)	M5
Class	8.8
Extra info	1 meter
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

NF	E25-136
DIN	976-1A

Technical Specification

P	0.80
---	------

Technical Drawing

