

Threaded rod length 1 meter DIN 976-1A Steel Zinc plated 8.8 M6



Article No.	20230.060.001
Brand	-
UBB	950353012418
UNSPSC	31161618
EAN	8715492605801
PKG. of 10	Full Box Only

Technical Parameters

Length (L) (mm)	1000
Diameter (d-D)	M6
Class	8.8
Extra info	1 meter
Material	Steel
Thread direction	Right
Surface treatment	Zinc plated
Thread	Metric thread

Standards

DIN	976-1A
NF	E25-136

Technical Specification

P	1
---	---

Technical Drawing

