



## Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B7 - Gr.2H 3/4X260 (10.1/4)

Article number	22080.191.260
Brand	-
UBB	951353842796
UNSPSC	31161619
EAN	8715493346796
PKG. of 1	Full Box Only

### Technical Parameters

Diameter	3/4 Inch
Length	260 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse
Threads per inch	10

#### Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

### Standards

ASTM	A193/A194
BS	≈4882
ASME	B16.5/B18.2.2

### Technical Specification

B	1.25
---	------

### Technical Drawing

L (mm)	260
M	18.7

