

Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Zinc plated Gr.B7 - Gr.2H 1/2X180 (7)



Article number	22082.127.177
Brand	-
UBB	500578451956
UNSPSC	31161619
EAN	8715494375139
PKG. of 1	Full Box Only

Technical Parameters

Diameter (inch)	1/2
Length (L) (mm)	180
Length (L) (Inch - ft)	7 Inch
Class	Gr.B7 - Gr.2H
Material	Steel
Surface treatment	Zinc plated
Thread direction	Right
Thread	Unified National Coarse
Material technical	ASTM A193 - ASTM A194

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3 L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASTM	A193/A194
ASME	B16.5/B18.2.2
BS	≈4882

Technical Specification

B	7/8
---	-----

Technical Drawing

M 12.3

Threads per inch 13

