



**Studbolt with 2 heavy
hexagon nuts ASME B16.5/
B18.2.2 Steel ASTM A193
- ASTM A194 Zinc plated
Gr.B7 - Gr.2H 3/4X75 (3)**

Article number	22082.191.076
Brand	-
UBB	500578457656
UNSPSC	31161619
EAN	8715494375702
PKG. of 1	Full Box Only

Technical Parameters

Diameter	3/4 Inch
Length	75 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Zinc plated
Thread	Unified National Coarse
Threads per inch	10

Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.
------	---

Standards

ASTM	A193/A194
ASME	B16.5/B18.2.2
BS	≈4882

Technical Specification

B	1.25
---	------

Technical Drawing

L (mm)	75
M	18.7

