



**Studbolt with 2 heavy  
hexagon nuts ASME B16.5/  
B18.2.2 Steel ASTM A193  
- ASTM A194 Zinc plated  
Gr.B7 - Gr.2H 1 Inch X170  
(6.3/4)**

Article number	22082.254.171
Brand	-
UBB	951353669611
UNSPSC	31161619
EAN	8715493206168
PKG. of 1	Full Box Only

**Technical Parameters**

Diameter	1 Inch
Length	170 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Zinc plated
Thread	Unified National Coarse
Threads per inch	8

Info  
Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

**Standards**

BS	≈4882
ASTM	A193/A194
ASME	B16.5/B18.2.2

B	1.625
L (mm)	170
M	25

