



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B7M - Gr.2HM 1/2X45 (1.3/4)

Article number	22085.127.044
Brand	-
UBB	500578756636
UNSPSC	31161619
EAN	8715494376594
PKG. of 1	Full Box Only

Technical Parameters

Diameter	1/2 Inch
Length	45 mm
Class	Gr.B7M - Gr.2HM
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse
Threads per inch	13

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASTM	A193/A194
ASME	B16.5/B18.2.2
BS	≈4882

Technical Specification

B	0.875
---	-------

Technical Drawing

L (mm)	45
M	12.3

