



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B7M - Gr.2HM 5/8X255 (10)

Article number	22085.158.254
Brand	-
UBB	500578764630
UNSPSC	31161619
EAN	8715494379892
PKG. of 1	Full Box Only

Technical Parameters

Diameter	5/8 Inch
Length	255 mm
Class	Gr.B7M - Gr.2HM
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse
Threads per inch	11

Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.
------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Standards

ASME	B16.5/B18.2.2
ASTM	A193/A194
BS	≈4882

Technical Specification

B	1.0625
---	--------

Technical Drawing

L (mm) 255

M 15.5

