



**Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B7M - Gr.2HM 3/4X360 (14.1/4)**

Article number	22085.191.361
Brand	-
UBB	500578772971
UNSPSC	31161619
EAN	8715494385695
PKG. of 1	Full Box Only

**Technical Parameters**

Diameter	3/4 Inch
Length	360 mm
Class	Gr.B7M - Gr.2HM
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse
Threads per inch	10

Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.
------	---

**Standards**

ASME	B16.5/B18.2.2
BS	≈4882
ASTM	A193/A194

**Technical Specification**

B	1.25
---	------

**Technical Drawing**

L (mm) 360

M 18.7

