



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B7M - Gr.2HM 3/4X370 (14.1/2)

Article number	22085.191.368
Brand	-
UBB	500578773136
UNSPSC	31161619
EAN	8715494385718
PKG. of 1	Full Box Only

Technical Parameters

Diameter	3/4 Inch
Length	370 mm
Class	Gr.B7M - Gr.2HM
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse
Threads per inch	10

Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.
------	---

Standards

BS	≈4882
ASTM	A193/A194
ASME	B16.5/B18.2.2

Technical Specification

B	1.25
---	------

Technical Drawing

L (mm) 370

M 18.7

