



**Studbolt with 2 heavy
hexagon nuts ASME B16.5/
B18.2.2 Steel ASTM A193 -
ASTM A194 Plain Gr.B7M -
Gr.2HM 1 Inch X340 (13.3/8)**

Article number	22085.254.340
Brand	-
UBB	500578788571
UNSPSC	31161619
EAN	8715494389723
PKG. of 1	Full Box Only

Technical Parameters

Diameter	1 Inch
Length	340 mm
Class	Gr.B7M - Gr.2HM
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse
Threads per inch	8

Info	Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.
------	---

Standards

ASME	B16.5/B18.2.2
BS	≈4882
ASTM	A193/A194

Technical Specification

B	1.625
---	-------

Technical Drawing

L (mm) 340

M 25

