

## Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B7M - Gr.2HM 1.1/4X510 (20)



Article number	22086.317.508
Brand	-
UBB	500578809526
UNSPSC	31161619
EAN	8715494381048
PKG. of 1	Full Box Only

### Technical Parameters

Diameter (inch)	1.1/4
Length (L) (mm)	510
Length (L) (Inch - ft)	20 Inch
Class	Gr.B7M - Gr.2HM
Material	Steel
Surface treatment	Plain
Thread direction	Right
Thread	8 Unified National
Material technical	ASTM A193 - ASTM A194

**Info**

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3 L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

### Standards

BS	≈4882
ASME	B16.5/B18.2.2
ASTM	A193/A194

### Technical Specification

B	2.IN.
M	31

### Technical Drawing

Threads per inch 8

**FABORY**

