

Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B7M - Gr.2HM 1.3/8X365 (14.3/8)



Article number	22086.349.365
Brand	-
UBB	500578815135
UNSPSC	31161619
EAN	8715494386579
PKG. of 1	Full Box Only

Technical Parameters

Diameter (inch)	1.3/8
Length (L) (mm)	365
Length (L) (Inch - ft)	14.3/8
Class	Gr.B7M - Gr.2HM
Material	Steel
Surface treatment	Plain
Thread direction	Right
Thread	8 Unified National
Material technical	ASTM A193 - ASTM A194

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3 L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASTM	A193/A194
ASME	B16.5/B18.2.2
BS	≈4882

Technical Specification

B	2.3/16
M	34.1

Technical Drawing

Threads per inch 8

FABORY

