



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Plain Gr.B7 - Gr.2H 1.1/8X105 (4.1/8)

Article number	22090.285.105
Brand	-
UBB	500578478371
UNSPSC	31161619
EAN	8715494364515
PKG. of 1	Full Box Only

Technical Parameters

Diameter	1.1/8 Inch
Length	105 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	8 Unified National
Threads per inch	8

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASME	B16.5/B18.2.2
ASTM	A193/A194
BS	≈4882

Technical Specification

B	1.8125
L (mm)	105

Technical Drawing

