



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A193 - ASTM A194 Zinc plated Gr.B7 - Gr.2H 1.1/8X130 (5.1/8)

Article number	22092.285.130
Brand	-
UBB	500578074683
UNSPSC	31161619
EAN	8715494311496
PKG. of 1	Full Box Only

Technical Parameters

Diameter (inch)	1.1/8
Length (L) (mm)	130
Length (L) (Inch - ft)	5.1/8

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3 L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Class	Gr.B7 - Gr.2H
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Zinc plated
Thread	8 Unified National

Standards

BS	≈4882
ASME	B16.5/B18.2.2
ASTM	A193/A194

Technical Specification

Technical Drawing

B	1.13/16
M	28.2
Threads per inch	8

