



**Studbolt with 2 heavy
hexagon nuts ASME B16.5/
B18.2.2 Steel ASTM A193
- ASTM A194 Zinc plated
Gr.B7 - Gr.2H 1.5/8X315
(12.1/2)**

Article number	22092.412.317
Brand	-
UBB	951353674983
UNSPSC	31161619
EAN	8715493206748
PKG. of 1	Full Box Only

Technical Parameters

Diameter	1.5/8 Inch
Length	315 mm
Class	Gr.B7 - Gr.2H
Material	Steel
Material technical	ASTM A193 - ASTM A194
Thread direction	Right
Surface treatment	Zinc plated
Thread	8 Unified National
Threads per inch	8

Info Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASTM	A193/A194
ASME	B16.5/B18.2.2
BS	≈4882

B	2.5625
L (mm)	315
M	40.5

