



Studbolt with 2 heavy hexagon nuts ASME B16.5/ B18.2.2 Steel ASTM A320 - ASTM A194 Plain Gr.L7 - Gr.7 1/2X70 (2.3/4)

Article number	22325.127.069
Brand	-
UBB	951353015708
UNSPSC	31161619
EAN	8715492621061
PKG. of 1	Full Box Only

Technical Parameters

Diameter	1/2 Inch
Length	70 mm
Class	Gr.L7 - Gr.7
Material	Steel
Material technical	ASTM A320 - ASTM A194
Thread direction	Right
Surface treatment	Plain
Thread	Unified National Coarse
Threads per inch	13

Info

Tolerances of the total length of the studbolts according to ASME B16.5 Table C-3L is the nominal length of the studbolt, measured from the first to the last full thread and thus excluding the chamfered ends.

Standards

ASME	B16.5/B18.2.2
ASTM	A193/A194
BS	≈4882

Technical Specification

B	0.875
---	-------

Technical Drawing

L (mm) 70

M 12.3

